



Standard Candle B35 frosted

230V 25W BC PEARL CANDLE


Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information		Mechanical and Housing	
Cap-Base	B22 [B22]	Bulb Finish	Frosted
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	B35 [B 35mm]
Nominal lifetime	1,000 hour(s)		
Rated Lifetime (Hours)	1,000 hour(s)		
Lighting Technology	Incandescent		
Light Technical		Product Data	
Luminous Flux	205 lm	Order product name	230V 25W BC PEARL CANDLE
Color rendering index (CRI)	100	Full product name	230V 25W BC PEARL CANDLE
		Full product code	890143700286000
		Order code	921485644299
		Material Nr. (12NC)	921485644299
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8901437002860
		Numerator - Packs per outer box	300
		EAN/UPC - Case	8727900076523
Operating and Electrical			
Power Consumption	25 W		
Voltage (Nom)	230 V		
Voltage (Nom)	230 V		
Controls and Dimming			
Dimmable	Yes		

Standard Candle B35 frosted

Dimensional drawing



Product	D	C (max)
230V 25W BC PEARL CANDLE	35 mm	95 mm

