



Standard Candle B35 frosted

230V 25W BC PEARL CANDLE


Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information		Mechanical and Housing	
Cap-Base	B22 [B22]	Bulb Finish	Frosted
Operating Position	UNIVERSAL [Universal]		
Nominal Lifetime (Nom)	1000 h		
Light Technical		Product Data	
Luminous Flux (Nom)	205 lm	Full product code	890143700286000
Color Rendering Index (Nom)	100	Order product name	230V 25W BC PEARL CANDLE
		EAN/UPC - Product	8901437002860
		Order code	921485644299
Operating and Electrical		Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	25 W	Numerator - Packs per outer box	300
Voltage (Nom)	230 V	Material Nr. (12NC)	921485644299
		Net Weight (Piece)	0.020 kg
Controls and Dimming		ILCOS Code	IBB/F-25-230-B22d-35
Dimmable	Yes		

Standard Candle B35 frosted

Dimensional drawing



Product

230V 25W BC PEARL CANDLE

CAN STD 25W B22 230V B35 FR

