

# CLASSICTONE Candle

## CLASSICTONE 25W E14 240V B35 CL 1CT/10X10F

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

### Product data

General Information	
Cap base	E14 [ E14]
Burning Position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	210 lm
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	25 W
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear


Approval and Application	
Energy efficiency label (EEL)	E

Product Data	
Full product code	871150022303650
Order product name	CLASSICTONE 25W E14 240V B35 CL 1CT/10X10F
EAN/UPC – product	8711500223036
Order code	921486545538
Local Code	C35CL25W240VSE
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (I2NC)	921486545538
Net weight (piece)	0.015 kg
ILCOS Code	IBB/C-25-240-E14-35

# CLASSICTONE Candle

## Dimensional drawing



Product	D	C (max)
CLASSICTONE 25W E14 240V B35 CL 1CT/10X10F	35 mm	100 mm

CAN STD 25W E14 240V B35 CL

