



Party Lustre P45

230V 15W DECORATION BLUE

Colored incandescent lamp with P45 shape and superior ESC coating

Product data


General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Universal]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Luminous Flux (Nom)	120 lm
Operating and Electrical	
Power (Rated) (Nom)	15 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Blue

Approval and Application	
Energy Efficiency Label (EEL)	G
Product Data	
Full product code	890143700228000
Order product name	230V 15W DECORATION BLUE
EAN/UPC - Product	8901437002280
Order code	921560044299
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	240
Material Nr. (12NC)	921560044299
Net Weight (Piece)	0.022 kg
ILCOS Code	IBP/B-15-230-B22d-45

Party Lustre P45

Dimensional drawing

Product	D	C (max)
230V 15W DECORATION BLUE	45 mm	71.5 mm



LUS COL 15W B22 230V P45 BL

