



Appliance Oven P45

APPL 40W E14 240V P45 CL OV 1BL/10

Lustre vacuum lamps with clear glass (P-bulb)


Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	420 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40.0 W
Lamp Current (Nom)	0.17 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45
Approval and Application	
Energy Consumption kWh/1000 h	40 kWh
Product Data	
Order product name	Appl 40W E14 240V P45 CL OV 1BL/10
Full product name	APPL 40W E14 240V P45 CL OV 1BL/10
Full product code	871150015754625
Order code	15754625
Material Nr. (12NC)	923265945508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500157546
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500158727

Appliance Oven P45

Dimensional drawing



Product	D	C (max)
Appl 40W E14 240V P45 CL OV 1BL/10	45 mm	75 mm

