



# Appliance Oven P45

## APPL 40W E14 240V P45 CL OV 1BL/10

Lustre vacuum lamps with clear glass (P-bulb)

### Product data

General Information	
Cap-Base	E14 [ E14]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Oven
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X

  

Light Technical	
Luminous Flux (Nom)	420 lm
Luminous Flux (Rated) (Nom)	420 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100

  

Operating and Electrical	
Power (Rated) (Nom)	40.0 W
Lamp Current (Nom)	0.17 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	240 V

  

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

  

Approval and Application	
Energy Efficiency Label	E
Energy Consumption kWh/1000 h	40 kWh

  

Product Data	
Full product code	871150015754625
Order product name	Appliance 40W E14 240V P45 CL OV 1BL/10
EAN/UPC - Product	8711500157546
Order code	15754625
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923265945508
Net Weight (Piece)	15.460 g
ILCOS Code	IBP/C-40-240-E14-45*

## Appliance Oven P45

### Dimensional drawing



APP 40W E14 240V P45 CL OV

Product	D	C (max)
Appliance 40W E14 240V P45 CL OV 1BL/10	45 mm	75 mm

