



SPOTONE Ring Mirror Spotline

SPOT 40W E27 220-240V NR63 30D FR 1CT

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]
Product Data	
Order product name	SPOT 40W E27 220-240V NR63 30D FR 1CT
Full product name	SPOT 40W E27 220-240V NR63 30D FR 1CT
Full product code	871150004360300
Order code	923339243326
Material Nr. (12NC)	923339243326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043603
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500233042

SPOTONE Ring Mirror Spotline

Dimensional drawing



Product	D
SPOT 40W E27 220-240V NR63 30D FR 1CT	63 mm

