



SPOTONE Ring Mirror Spotline

REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F


Reflector lamps based on advanced spotlighting technology

Product data

General Information		Mechanical and Housing	
Cap-Base	E27 [E27]	Bulb Finish	Frosted
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	NR63 [NR 63mm]
Nominal lifetime	1,000 h	Product Data	
Rated Lifetime (Hours)	1,000 h	Order product name	REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F
Lighting Technology	Incandescent	Full product name	REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F
Light Technical		Full product code	871150017130600
Beam Angle (Nom)	30 degree(s)	Order code	923339245520
Color rendering index (CRI)	100	Material Nr. (12NC)	923339245520
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	EAN/UPC - Product/Case	8711500171306
Voltage (Nom)	240 V	Numerator - Packs per outer box	12
Voltage (Nom)	240 V	EAN/UPC - Case	8727900844184
Controls and Dimming			
Dimmable	Yes		

SPOTONE Ring Mirror Spotline

Dimensional drawing



Product	D
REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F	63 mm

