



# Reflector diam 63 mm

## REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F

Reflector lamps based on advanced spotlighting technology


### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]
Product Data	
Order product name	REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F
Full product name	REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F
Full product code	871150017082800
Order code	923339445558
Material Nr. (12NC)	923339445558
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500170828
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900844153


Reflector diam 63 mm

Dimensional drawing



Product	D
REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F	63 mm

Photometric data



Light Distribution Diagram - REF SPOT 60W E27 240V NR63 30DFR2CT/4X3F

