



InfraRed Industrial Heat Incandescent

PAR38 IR 100W E27 240V Red 1CT/12

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.


Product data

General Information	
Cap base	E27 [E27]
Burning Position	H45 [h45]
Main application	Infrared Industrial
Nominal lifetime (nom.)	5000 h
Light Technical	
Colour Designation	R
Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Red
Bulb material	Hard Glass
Product Data	
Full product code	871150012891115
Order product name	PAR38 IR 100W E27 240V Red 1CT/12
EAN/UPC – product	8711500128911
Order code	923801145506
Local Code	IRPAR38100WR
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	923801145506
Net weight (piece)	308.000 g

InfraRed Industrial Heat Incandescent

Dimensional drawing



PAR38 IR 100W E27 240V Red

Product

PAR38 IR 100W E27 240V Red 1CT/12

