



Reflector Infrared BR40, PAR38

IR175R/PAR 120V 12/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General Information		Mechanical and Housing	
Base	E26 [Single Contact Medium Screw]	Bulb Finish	Red
Operating Position	H45 [h45]	Bulb Material	Hard Glass
Main Application	Infrared Industrial		
Nominal Lifetime (Nom)	5000 h		
Light Technical		Product Data	
Color Designation	R	Order product name	IR175R/PAR 120V 12/1
		EAN/UPC - Product	046677116279
		Order code	232306
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	12
		Material Nr. (12NC)	923813634608
		Net Weight (Piece)	308.000 g
Operating and Electrical			
Power (Rated) (Nom)	175 W		
Voltage (Nom)	115-125 V		
Controls and Dimming			
Dimmable	Yes		

Reflector Infrared BR40,PAR38

Dimensional drawing



Product

IR175R/PAR 120V 12/1

IR175R PAR38 175W E26 115-125V

