



PAR38

PAR38 120W E27 240V FL 1CT/6

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Product data

General Information	
Cap-Base	E27/51 [E27/51]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Luminous Flux	1,150 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	120 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	220-240 V

Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Product Data	
Order product name	PAR38 120W E27 240V FL 1CT/6
Full product name	PAR38 120W E27 240V FL 1CT/6
Full product code	871016317089300
Order code	923815645594
Material Nr. (12NC)	923815645594
Local order code	PAR38FL120W240
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163170893
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163170947


PAR38

Dimensional drawing



Product	D	C (max)	C1
PAR38 120W E27 240V FL 1CT/6	121 mm	137 mm	123 mm

Photometric data



Light Distribution Diagram - PAR38 120W E27 240V FL 1CT/6

