



PAR38

PAR38 120W E27 115V SP 1CT/12

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Product data

General Information	
Cap-Base	E27/51 [E27/51]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	12 degree(s)
Correlated Color Temperature (Nom)	2700 K
Operating and Electrical	
Power Consumption	120 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	115 V
Voltage (Nom)	115 V

Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Product Data	
Order product name	PAR38 120W E27 115V SP 1CT/12
Full product name	PAR38 120W E27 115V SP 1CT/12
Full product code	871016314426900
Order code	923822334481
Material Nr. (12NC)	923822334481
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163144269
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696686058


PAR38

Dimensional drawing



Product	D	C (max)
PAR38 120W E27 115V SP 1CT/12	121 mm	134 mm

Photometric data



Light Distribution Diagram - PAR38 120W E27 115V SP 1CT/12

