

Halogen non-reflector

7027 50W G6.35 12V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

General Information	
Cap base	G6.35
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% failures (nom.)	50 h

Light Technical	
Colour rendering index (CRI)	100


Operating and Electrical	
Power Consumption	50 W
Voltage (nom.)	12 V
Voltage (nom.)	12 V

Mechanical and Housing	
Bulb material	Quartz-UV Open

Product Data	
Order product name	7027 50W G6.35 12V 1CT/10X10F
Full product name	7027 50W G6.35 12V 1CT/10X10F
Full EOC	871150040982950
Order code	40982950
Material no. (12 NC)	923870217103
Local order code	A1220
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500409829
Numerator – packs per outer box	100
EAN/UPC - Case	8711500423245

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7027 50W G6.35 12V 1CT/10X10F	11.5 mm	29.75 mm	30.25 mm	30 mm	1.05 mm	1 mm	0.95 mm	44 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.