PHILIPS Lighting



Halogen non-reflector

6550 150W G6.35 15V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

General Information					
Cap base	G6.35 [G6.35]				
Operating position	S90 [Standing +/-90D or Base Down (BDH)]				
Life to 50% failures (nom.)	50 h				
Light Technical					
Correlated Colour Temperature	3450 K				
Colour rendering index (CRI)	100				
Operating and Electrical					
Power Consumption	150 W				
Voltage (nom.)	15 V				
Voltage (nom.)	15 V				
Mechanical and Housing					
Bulb material	Quartz-UV Open				

Product Data	
Order product name	6550 150W G6.35 15V 1CT/10X10F
Full product name	6550 150W G6.35 15V 1CT/10X10F
Full EOC	871150040984350
Order code	40984350
Material no. (12 NC)	923870618503
Local order code	A1234
SAP numerator – quantity per pack	1
EAN/UPC - Product/Case	8711500409843
Numerator – packs per outer box	100
EAN/UPC - Case	8711500423184

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	Р	P (min)	C (max)
6550 150W	11.5 mm	29.75	30.25	30	1.05 mm	1 mm	0.95	44 mm
G6.35 15V		mm	mm	mm			mm	
1CT/10X10F								



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 30 - data subject to change