



Halogen non-reflector

6550 150W G6.35 15V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

General Information	
Cap-Base	G6.35 [G6.35]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	50 hour(s)

Light Technical	
Correlated Color Temperature (Nom)	3450 K
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	15 V
Voltage (Nom)	15 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	6550 150W G6.35 15V 1CT/10X10F
Full product name	6550 150W G6.35 15V 1CT/10X10F
Full product code	871150040984350
Order code	923870618503
Material Nr. (12NC)	923870618503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409843
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423184

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
6550 150W	11.5 mm	29.75	30.25	30	1.05 mm	1 mm	0.95	44 mm
G6.35 15V		mm	mm	mm			mm	
1CT/10X10F								

