



# Halogen non-reflector

## 7724 100W GY6.35 12V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information	
Cap-Base	GY6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3300 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	7724 EVA 100W GY6.35 12V
Full product name	7724 100W GY6.35 12V 1CT/10X10F
Full product code	871150040985050
Order code	40985050
Material Nr. (12NC)	923872517103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409850
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423276

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7724 EVA	10.7 mm	29.65	30.25	30	1.30 mm	1.25	1.20 mm	44 mm
100W		mm	mm	mm		mm		
GY6.35 12V								

