



Halogen non-reflector

7724 EVA 100W GY6.35 12V

Low-voltage quartz halogen capsule lamps

Product data

| General Information | |
|----------------------------|--|
| Cap-Base | GY6.35 [GY6.35] |
| Operating Position | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom) | 2,000 h |

| Light Technical | |
|------------------------------------|--------|
| Correlated Color Temperature (Nom) | 3300 K |
| Color rendering index (CRI) | 100 |


| Operating and Electrical | |
|--------------------------|-------|
| Power Consumption | 100 W |
| Voltage (Nom) | 12 V |
| Voltage (Nom) | 12 V |

| Mechanical and Housing | |
|------------------------|----------------|
| Bulb Material | Quartz-UV Open |

| Product Data | |
|---------------------------------|--------------------------|
| Order product name | 7724 EVA 100W GY6.35 12V |
| Full product name | 7724 EVA 100W GY6.35 12V |
| Full product code | 871150040985050 |
| Local code description | 7724 |
| Order code | 923872517103 |
| Material Nr. (12NC) | 923872517103 |
| Local order code | 7724 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500409850 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500423276 |

Halogen non-reflector

Dimensional drawing



| Product | D (max) | L (min) | L (max) | L | P (max) | P | P (min) | C (max) |
|------------|---------|---------|---------|----|---------|------|---------|---------|
| 7724 EVA | 10.7 mm | 29.65 | 30.25 | 30 | 1.30 mm | 1.25 | 1.20 mm | 44 mm |
| 100W | | mm | mm | mm | | mm | | |
| GY6.35 12V | | | | | | | | |

