



# Halogen non-reflector

## 7724 EVA 100W GY6.35 12V

Low-voltage quartz halogen capsule lamps

### Product data

General Information	
Cap-Base	GY6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3300 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	7724 EVA 100W GY6.35 12V
Full product name	7724 EVA 100W GY6.35 12V
Full product code	871150040985050
Order code	923872517103
Material Nr. (12NC)	923872517103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409850
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423276

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7724 EVA	10.7 mm	29.65	30.25	30	1.30 mm	1.25	1.20 mm	44 mm
100W		mm	mm	mm		mm		
GY6.35 12V								

