



# Halogen non-reflector

## 6605 10W G4 6V 1CT/10X10F

Low-voltage quartz halogen capsule lamps


### Product data

General Information	
Cap-Base	G4 [G4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Luminous Flux	150 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	10 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Product Data	
Order product name	6605 10W G4 6V 1CT/10X10F
Full product name	6605 10W G4 6V 1CT/10X10F
Full product code	871150041009250
Order code	923873910103
Material Nr. (12NC)	923873910103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410092
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423320

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
6605 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

