



# Halogen non-reflector

## 7387 10W G4 6V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

### Product data

General Information	
Cap-Base	G4 [G4]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	100 hour(s)

Light Technical	
Luminous Flux	200 lm
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	10 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V


  

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	7387 10W G4 6V 1CT/10X10F
Full product name	7387 10W G4 6V 1CT/10X10F
Full product code	871150041027650
Order code	923874510103
Material Nr. (12NC)	923874510103
Local order code	7387
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410276
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423313

## Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (max)	C (max)
7387 10W G4 6V ICT/10X10F	9.5 mm	19.75 mm	31 mm

