



Halogen non-reflector

7387 10W G4 6V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data


General Information			
Cap-Base	G4 [G4]		
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]		
Life to 50% Failures (Nom)	100 hour(s)		
Light Technical			
Luminous Flux	200 lm		
Correlated Color Temperature (Nom)	3200 K		
Color rendering index (CRI)	100		
Operating and Electrical			
Power Consumption	10 W		
Voltage (Nom)	6 V		
Voltage (Nom)	6 V		

Mechanical and Housing			
Bulb Material	Quartz-UV Open		
Product Data			
Order product name	7387 10W G4 6V 1CT/10X10F		
Full product name	7387 10W G4 6V 1CT/10X10F		
Full product code	871150041027650		
Order code	923874510103		
Material Nr. (12NC)	923874510103		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8711500410276		
Numerator - Packs per outer box	100		
EAN/UPC - Case	8711500423313		

Datasheet, 2023, April 16 data subject to change

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
7387 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.