



Halogen non-reflector

7388 20W G4 6V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

| General Information | |
|-----------------------------|----------------------------|
| Cap base | G4 [G4] |
| Philips code | 7388 |
| ANSI Code | ESB |
| LIF code | M30 |
| Burning Position | UNIVERSAL [Any/Universal] |
| Main application | Projection |
| Life to 50% failures (nom.) | 100 h |

| Light Technical | |
|------------------------------------|--------|
| Lamp Luminous Flux 25°C EL (Nom) | 460 lm |
| Colour Rendering Index,horiz (Nom) | 100 |

| Operating and Electrical | |
|--------------------------|------|
| Power (Rated) (Nom) | 20 W |
| Voltage (Nom) | 6 V |

| Mechanical and Housing | |
|------------------------|----------------|
| Bulb material | Quartz-UV Open |


| | |
|-------------------------|---------|
| Filament dimensions WxH | 2.3x0.8 |
|-------------------------|---------|

| Luminaire Design Requirements | |
|-------------------------------|--------|
| Bulb temperature (max.) | 900 °C |
| Pinch temperature (max.) | 400 °C |

| Product Data | |
|---------------------------------|---------------------------|
| Full product code | 871150040986750 |
| Order product name | 7388 20W G4 6V 1CT/10X10F |
| EAN/UPC – product | 8711500409867 |
| Order code | 923874610103 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 100 |
| Material no. (12NC) | 923874610103 |
| Net weight (piece) | 0.001 kg |

Halogen non-reflector

Dimensional drawing



| Product | D (max) | L (max) | C (max) |
|---------------------------|---------|----------|---------|
| 7388 20W G4 6V 1CT/10X10F | 9.5 mm | 19.75 mm | 31 mm |

7388 20W G4 6V

