



Halogen non-reflector

ESB 7388 20W 6V 100PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

| General Information | |
|----------------------------|------------------------|
| Base | G4 [G4] |
| Philips Code | 7388 |
| ANSI Code | ESB |
| LIF Code | M30 |
| Operating Position | Universal [Universal] |
| Main Application | Projection |
| Life to 50% Failures (Nom) | 100 h |

| Light Technical | |
|------------------------------------|--------|
| Initial lumen (Nom) | 460 lm |
| Correlated Color Temperature (Nom) | 3350 K |
| Color Rendering Index (Nom) | 100 |

| Operating and Electrical | |
|--------------------------|------|
| Power (Rated) (Nom) | 20 W |
| Voltage (Nom) | 6 V |


| Mechanical and Housing | |
|-------------------------|----------------|
| Bulb Material | Quartz-UV Open |
| Filament Dimensions WxH | 2.3x0.8 |

| Luminaire Design Requirements | |
|-------------------------------|--------|
| Bulb Temperature (Max) | 900 °C |
| Pinch Temperature (Max) | 400 °C |

| Product Data | |
|---------------------------------|---------------------------|
| Order product name | 7388 20W G4 6V 1CT/10X10F |
| EAN/UPC - Product | 8711500409867 |
| Order code | 256784 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 100 |
| Material Nr. (12NC) | 923874610103 |
| Net Weight (Piece) | 0.001 kg |

Halogen non-reflector

Dimensional drawing



| Product | D (max) | L (max) | C (max) |
|---------------------------|---------|----------|---------|
| 7388 20W G4 6V 1CT/10X10F | 9.5 mm | 19.75 mm | 31 mm |

7388 20W G4 6V

