



Halogen reflector

13528 15W GZ4 6V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system


Product data

General Information	
Cap-Base	GZ4 [GZ4]
Operating Position	S105 [s105]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Bulb Shape	R35 [R 35mm]
Product Data	
Order product name	13528 15W GZ4 6V 1CT/24
Full product name	13528 15W GZ4 6V 1CT/24
Full product code	871869668993600
Order code	923883810105
Material Nr. (12NC)	923883810105
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696689936
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696689943

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
13528 15W GZ4 6V 1CT/24	35 mm	42 mm

