



Halogen reflector

13528 15W GZ4 6V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


Product data

General Information		Controls and Dimming	
Cap-Base	GZ4 [GZ4]	Dimmable	Yes
Operating Position	S105 [s105]		
Life to 50% Failures (Nom)	750 hour(s)		
Light Technical		Mechanical and Housing	
Correlated Color Temperature (Nom)	2900 K	Bulb Material	Quartz-UV Open
Color rendering index (CRI)	100	Reflector Finish	Smooth
		Bulb Shape	R35 [R 35mm]
Operating and Electrical		Product Data	
Power Consumption	15 W	Order product name	13528 15W GZ4 6V 1CT/24
Voltage (Nom)	6 V	Full product name	13528 15W GZ4 6V 1CT/24
Voltage (Nom)	6 V	Full product code	871869668993600
		Order code	324038
		Material Nr. (12NC)	923883810105
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696689936

Halogen reflector

Numerator - Packs per outer box	24
EAN/UPC - Case	8718696689943

Dimensional drawing



Product	D (max)	C (max)
13528 15W GZ4 6V 1CT/24	1-3/8 inch	1-11/16 inch

