



# Halogen reflector

## 6834 100W GZ6.35 12V

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system


### Product data

General Information	
Cap-Base	GZ6.35 [GZ6.35]
Operating Position	P90/P15
Life to 50% Failures (Nom)	50 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3330 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Reflector Finish	Smooth
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	6834 100W GZ6.35 12V
Full product name	6834 100W GZ6.35 12V
Full product code	871150042731160
Order code	923916717104
Material Nr. (12NC)	923916717104
Local order code	6834
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500427311
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500427328

# Halogen reflector

## Dimensional drawing



Product	D (max)	C (max)
6834 100W GZ6.35 12V	50 mm	42 mm

