



Halogen reflector

6423 150W GZ6.35 15V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

产品数据


一般信息	
底盖	GZ6.35 [GZ6.35]
操作位置	P90/P15
50% 故障条件下的使用寿命 (标称)	50 小时
灯技术	
相关色温 (标称)	3380 K
显色指数 (CRI)	100
操作和电气	
功耗	150 W
电压 (标称)	15 V
电压 (标称)	15 V

控制和调光	
可调光	是
机械和外壳	
灯泡材料	开放紫外线石英
反射器外观	光滑
灯泡外形	R50 [R 50 毫米]
产品数据	
订单产品名称	6423 150W GZ6.35 15V 1CT/10X5F
完整的产品名称	6423 150W GZ6.35 15V 1CT/10X5F
完整产品代码	871150042733560
订购代码	923916818504
材料编号 (12NC)	923916818504
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500427335

Halogen reflector

计算器 - 每个外包装箱中的包数	50
EAN/UPC - 案例	8711500427342

二维绘图



Product	D (max)	C (max)
6423 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

