



# Plusline Compact

## Plusline C 150W R7s 240V 1BC/12

Mains-voltage linear lamp giving white halogen light


### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	2,400 lm
Luminous Efficacy (rated) (Nom)	16 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Lamp Current (Nom)	0.63 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Order product name	Plusline C 150W R7s 240V 1BC/12
Full product name	Plusline C 150W R7s 240V 1BC/12
Full product code	871150090174300
Order code	923919945709
Material Nr. (12NC)	923919945709
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500901743
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291225454

# Plusline Compact

## Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 150W R7s 240V 1BC/12	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

