



Plusline Compact

Plusline C 100W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light


Product data

Informasi Umum	
Tutup-Dasar	R7S [R7s]
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	2.000 jam
Nilai Masa Pakai (Jam)	2.000 jam
Teknologi Pencahayaan	Halogen
Teknis Lampu	
Flux Cahaya	1.550 lm
Suhu Warna Terkorelasi (Nom)	2800 K
Daya Penerangan (terukur) (Nom)	15,5 lm/W
Indeks renderasi warna (CRI)	100
Pengoperasian dan Kelistrikan	
Konsumsi Daya	100 W
Arus Lampu (Nom)	0,43 A
Waktu Mulai (Nom)	0,0 s
Tegangan (Nom)	230 V
Tegangan (Nom)	230 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya
Mekanis dan Housing	
Lapisan bohlam	Bening
Bentuk Bohlam	T3 [T 12mm (T3)]
Data Produk	
Nama produk pesanan	Plusline C 100W R7s 230V 1CT/10X10F
Nama lengkap produk	Plusline C 100W R7s 230V 1CT/10X10F
Kode produk lengkap	872790080839100
Kode urutan	923920043242
No. Material (12NC)	923920043242
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8727900808391
Numerator - Pak per kotak bagian luar	100
EAN/UPC - Kantung	8727900808407

Plusline Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 100W R7s 230V 1CT/10X10F	12 mm	76,5 mm	74,9 mm	73,3 mm	78 mm

