



Plusline Compact

PLUS PRO C 100W R7s 230V T3 CL 1BC

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	1,550 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	15.5 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	100 W
Lamp Current (Nom)	0.43 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]

Product Data	
Order product name	PLUS PRO C 100W R7s 230V T3 CL 1BC
Full product name	PLUS PRO C 100W R7s 230V T3 CL 1BC
Full product code	871150088538800
Order code	923920043280
Material Nr. (12NC)	923920043280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500885388
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500885579

Plusline Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO C 100W R7s 230V T3 CL 1BC	12 mm	76.5 mm	74.9 mm	73.3 mm	78 mm

