



Halogen reflector

5995 EJM 150W GX5.3 21V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	40 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	21 V
Voltage (Nom)	21 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Product Data	
Order product name	5995 EJM 150W GX5.3 21V 1CT/24
Full product name	5995 EJM 150W GX5.3 21V 1CT/24
Full product code	871150041063430
Order code	923921019894
Material Nr. (12NC)	923921019894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410634
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419033

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
5995 EJM 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

