

Halogen reflector

5995 EJM 150W GX5.3 21V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	40 hour(s)

Light Technical	
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	21 V
Voltage (Nom)	21 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth

Product Data	
Order product name	5995 EJM 150W GX5.3 21V 1CT/24
Full product name	5995 EJM 150W GX5.3 21V 1CT/24
Full product code	871150041063430
Order code	923921019894
Material Nr. (12NC)	923921019894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410634
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419033

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
5995 EJM 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.