



Halogen reflector

DDL 150W 20V 24PK

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S105 [s105]
Life to 50% Failures (Nom)	500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3150 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	20 V
Voltage (Nom)	20 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Facetted reflector
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	DDL 150W 20V 24PK
Full product name	DDL 150W 20V 24PK
Full product code	871150041061030
Order code	923921419794
Material Nr. (12NC)	923921419794
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410610
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419002

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

