



# Halogen non-reflector

## 5761 30W G4 6V

Low-voltage quartz halogen capsule lamps


### Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 h
Light Technical	
Luminous Flux	765 lm
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	30 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	5761 30W G4 6V
Full product name	5761 30W G4 6V
Full product code	871150041084950
Local code description	5761
Order code	923931110103
Material Nr. (12NC)	923931110103
Local order code	5761
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410849
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423344

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (max)	C (max)
5761 30W G4 6V	9.5 mm	19.75 mm	31 mm

