



Halogen non-reflector

5761 30W G4 6V

Low-voltage quartz halogen capsule lamps


Product data

General Information	
Cap-Base	G4 [G4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 hour(s)
Light Technical	
Luminous Flux	765 lm
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	30 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Product Data	
Order product name	5761 30W G4 6V
Full product name	5761 30W G4 6V
Full product code	871150041084950
Order code	923931110103
Material Nr. (12NC)	923931110103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410849
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423344

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
5761 30W G4 6V	9.5 mm	19.75 mm	31 mm

