



Plusline Large (double ended)

Plusline Large 1500W R7s 230V 1CT/10

Mains-voltage linear with a coiled-coil filament, giving white halogen light


Product data

General Information	
Cap-Base	R7s
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	33,000 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	22 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	1,500.0 W
Lamp Current (Nom)	6.52 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11
Approval and Application	
Energy Consumption kWh/1000 h	1500 kWh
Product Data	
Order product name	Plusline L 1500W R7s 230V 1CT/10
Full product name	Plusline Large 1500W R7s 230V 1CT/10
Full product code	871150049435101
Order code	49435101
Material Nr. (12NC)	923932243203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500494351
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291720836

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

