



Plusline Large

Plusline L 1500W R7s 230V 1CT/10

Mains-voltage linear lamp giving white halogen light


Product data

Informasi Umum	
Tutup-Dasar	R7s
Posisi Pengoperasian	P4 [Sejajar +/-4D atau Horizontal(HOR)]
Nominal masa pakai	2.000 jam
Siklus Sakelar	8.000
Nilai Masa Pakai (Jam)	2.000 jam
Teknologi Pencahayaan	Halogen
Teknis Lampu	
Flux Cahaya	33.000 lm
Suhu Warna Terkorelasi (Nom)	2900 K
Daya Penerangan (terukur) (Nom)	22 lm/W
Indeks renderasi warna (CRI)	100
Pengoperasian dan Kelistrikan	
Konsumsi Daya	1.500,0 W
Arus Lampu (Nom)	6,52 A
Waktu Mulai (Nom)	0,0 s
Waktu pemanasan hingga 60% cahaya	cahaya penuh seketika s
Faktor Daya (Fraksi)	1
Tegangan (Nom)	230 V
Tegangan (Nom)	230 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya
Mekanis dan Housing	
Lapisan bohlam	Bening
Bentuk Bohlam	T11
Penyetujuan dan Aplikasi	
Penggunaan Energi kWh/1000 h	1500 kWh
Data Produk	
Nama produk pesanan	Plusline L 1500W R7s 230V 1CT/10
Nama lengkap produk	Plusline L 1500W R7s 230V 1CT/10
Kode produk lengkap	872790080857500
Kode urutan	923932243241
No. Material (12NC)	923932243241
Kode urutan lokal	PLUSLINE1500W23
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8727900808575
Numerator - Pak per kotak bagian luar	10
EAN/UPC - Kantung	8727900808582

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1500W R7s 230V 1CT/10	11 mm	252,3 mm	250,7 mm	249,1 mm	254,1 mm

