



Halogen non-reflector

7748XHP 250W G6.35 24V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

General Information	
Cap base	G6.35
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% failures (nom.)	50 h
Light Technical	
Correlated Colour Temperature	3550 K
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	250 W
Voltage (nom.)	24 V
Voltage (nom.)	24 V
Mechanical and Housing	
Bulb material	Quartz-UV Open

Product Data	
Order product name	7748XHP EHJ-S 250W G6.35 24V
Full product name	7748XHP 250W G6.35 24V 1CT/10X10F
Full EOC	871150041029050
Order code	41029050
Material no. (12 NC)	924006520503
Local order code	A1223X
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500410290
Numerator – packs per outer box	100
EAN/UPC – Case	8711500423153

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7748XHP EHJ-	12.5 mm	32.75	33.25	33	1.05 mm	1 mm	0.95	55 mm
S 250W G6.35		mm	mm	mm			mm	
24V								

