



# Halogen non-reflector

## 7748XHP EHJ-S 250W G6.35 24V

Low-voltage quartz halogen capsule lamps

#### **Product data**


General Information					
Cap-Base	G6.35 [G6.35]				
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]				
Life to 50% Failures (Nom)	50 hour(s)				
Light Technical					
Correlated Color Temperature (Nom)	3550 K				
Color rendering index (CRI)	100				
Operating and Electrical					
Power Consumption	250 W				
Voltage (Nom)	24 V				
Voltage (Nom)	24 V				
Mechanical and Housing					
Bulb Material	Quartz-UV Open				

Product Data					
Order product name	7748XHP EHJ-S 250W G6.35 24V				
Full product name	7748XHP EHJ-S 250W G6.35 24V				
Full product code	871150041029050				
Order code	924006520503				
Material Nr. (12NC)	924006520503				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8711500410290				
Numerator - Packs per outer box	100				
EAN/UPC - Case	8711500423153				

Datasheet, 2023, April 16 data subject to change

# Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	Р	P (min)	C (max)
7748XHP EHJ-	12.5 mm	32.75	33.25	33	1.05 mm	1 mm	0.95	55 mm
S 250W G6.35		mm	mm	mm			mm	
24V								

