



# Halogen reflector

## 13629 150W GX5.3 21V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system


### Product data

General Information	
Cap-Base	GX5.3
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	200 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	21 V
Voltage (Nom)	21 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Product Data	
Order product name	13629 150W GX5.3 21V 1CT/24
Full product name	13629 150W GX5.3 21V 1CT/24
Full product code	871150041073330
Order code	924010319894
Material Nr. (12NC)	924010319894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410733
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500421616

## Halogen reflector

### Dimensional drawing



Product	D (max)	C (max)
13629 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

