



# Halogen non-reflector

## 7158XHP 150W G6.35 24V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

### Product data

General Information	
Cap-Base	G6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	40 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3450 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	24 V
Voltage (Nom)	24 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	7158XHP 150W G6.35 24V 1CT/10X10F
Full product name	7158XHP 150W G6.35 24V 1CT/10X10F
Full product code	871150041020750
Order code	924031720503
Material Nr. (12NC)	924031720503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410207
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423221

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7158XHP 150W	11.5 mm	31.5 mm	33.25	33	1.05 mm	1 mm	0.95	50 mm
G6.35 24V			mm	mm			mm	
1CT/10X10F								

