



Capsuleline

CAPS 10W G4 12V CL 4000H 1CT/10X10F


Single-ended low-voltage halogen capsule giving crisp white halogen light

Product data

| General Information | |
|----------------------------------|----------------------------------|
| Cap base | G4 [G4] |
| Operating position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 4,000 h |
| Switching Cycle | 16,000 |
| Rated Lifetime (Hours) | 4,000 h |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 140 lm |
| Luminous efficacy (rated) (nom.) | 14 lm/W |
| Colour rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 10.0 W |
| Lamp current (nom.) | 0.83 A |
| Starting time (nom.) | 0.0 s |
| Warm-up time to 60% light | Instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (nom.) | 12 V |
| Voltage (nom.) | 12 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------------------|-------------------------------------|
| Lamp Finish | Clear |
| Bulb shape | T9 [T 9 mm (T9)] |
| Approval and Application | |
| Energy consumption kWh/1,000 hours | 11 kWh |
| Product Data | |
| Order product name | Caps 10W G4 12V CL 4000h 1CT/10X10F |
| Full product name | CAPS 10W G4 12V CL 4000H 1CT/10X10F |
| Full EOC | 871150040970650 |
| Order code | 40970650 |
| Material no. (12 NC) | 924036317101 |
| Local order code | 13284Q |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500409706 |
| Numerator – packs per outer box | 100 |
| EAN/UPC - Case | 8711500425645 |

Dimensional drawing



| Product | D (max) | L | C (max) |
|-------------------------------------|---------|-------|---------|
| Caps 10W G4 12V CL 4000h 1CT/10X10F | 9 mm | 22 mm | 33 mm |

