



Capsuleline

CAPS 10W G4 12V CL 4000H 1CT/10X10F

Single-ended low-voltage halogen capsule giving crisp white halogen light


Product data

General Information	
Cap base	G4 [G4]
Philips code	13284
Operating position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	4000 h
Switching cycle	16000X
Light Technical	
Luminous flux (nom.)	140 lm
Luminous flux (rated) (nom.)	140 lm
Correlated colour temperature (nom.)	2850 K
Luminous efficacy (rated) (nom.)	14 lm/W
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	10.0 W
Lamp current (nom.)	0.83 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Cap base information	na [-]
Approval and Application	
Energy efficiency label (EEL)	C
Energy Consumption kWh/1000 h	11 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Product Data	
Full product code	871150040970650
Order product name	Capsuleline 10W G4 12V CL 4000h 1CT/10X10F
EAN/UPC – product	8711500409706
Order code	40970650
Local Code	13284Q
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	924036317101
Net weight (piece)	1.200 g
ILCOS Code	HSG/C/UB-10-12-G4

Capsuleline

Dimensional drawing



Product	D (max)	L	C (max)
Capsuleline 10W G4 12V CL 4000h 1CT/10X10F	9 mm	22 mm	33 mm

CAP SU 13284 10W G4 12V CL

