



Halogen reflector

6423FO 150W GZ6.35 15V 1CT/10X5F

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap base	GZ6.35 [GZ6.35]
Philips code	6423FO
ANSI Code	EFR
LIF code	A1/232
Burning Position	P90/P15
Main application	Projection
Life to 50% failures (nom.)	50 h
J code	-

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	840 lm
Colour Temperature, horizontal (Nom)	3380 K
Colour Rendering Index, horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	15 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	na [-]

Bulb material	Quartz-UV Open
Reflector finish	-
Filament shape	-
Filament dimensions WxH	-

Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Working distance WD	32 mm

Product Data	
Full product code	871150040971360
Order product name	6423FO 150W GZ6.35 15V 1CT/10X5F
EAN/UPC – product	8711500409713
Order code	924048218504
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	924048218504
Net weight (piece)	0.024 kg

Halogen reflector

Dimensional drawing



6423FO 150W GZ6.35 15V

Product

6423FO 150W GZ6.35 15V 1CT/10X5F

