



Halogen reflector

6423FO 150W GZ6.35 15V 1CT/10X5F

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system


Product data

General Information	
Cap-Base	GZ6.35
Operating Position	P90/P15
Life to 50% Failures (Nom)	50 hour(s)
Light Technical	
Luminous Flux	840 lm
Correlated Color Temperature (Nom)	3380 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	15 V
Voltage (Nom)	15 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	-
Bulb Shape	R50
Product Data	
Order product name	6423FO 150W GZ6.35 15V 1CT/10X5F
Full product name	6423FO 150W GZ6.35 15V 1CT/10X5F
Full product code	871150040971360
Order code	924048218504
Material Nr. (12NC)	924048218504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409713
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500419231

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
6423FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

