



Halogen reflector

6834FO 100W GZ6.35 12V 1CT/10X5F

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data


General Information	
Cap-Base	GZ6.35
Operating Position	P90/P15
Life to 50% Failures (Nom)	50 h
Light Technical	
Correlated Color Temperature (Nom)	3330 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Reflector Finish	-	
Bulb Shape	R50	
Product Data		
Order product name	6834FO 100W GZ6.35 12V 1CT/10X5F	
Full product name	6834FO 100W GZ6.35 12V 1CT/10X5F	
Full product code	871150040973760	
Local code description	6834	
Order code	924048417104	
Material Nr. (12NC)	924048417104	
Local order code	6834	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500409737	
Numerator - Packs per outer box	50	
EAN/UPC - Case	8711500419392	

Datasheet, 2023, April 16 data subject to change

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
6834FO 100W GZ6.35 12V 1CT/10X5F	50 mm	42 mm

