



Halogen reflector

6834FO 100W GZ6.35 12V 1CT/10X5F

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap base	GZ6.35
Operating position	P90/P15
Life to 50% failures (nom.)	50 h
Light Technical	
Correlated Colour Temperature	3330 K
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (nom.)	12 V
Voltage (nom.)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb material	Quartz-UV Open

Reflector finish	-
Bulb shape	R50 [R 50 mm]
Product Data	
Order product name	6834FO 100W GZ6.35 12V 1CT/10X5F
Full product name	6834FO 100W GZ6.35 12V 1CT/10X5F
Full EOC	871150040973760
Order code	40973760
Material no. (12 NC)	924048417104
Local order code	A1231
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500409737
Numerator – packs per outer box	50
EAN/UPC – Case	8711500419392

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
6834FO 100W GZ6.35 12V 1CT/10X5F	50 mm	42 mm

