



Essential LV MR16

Ess MR16 35W GU5.3 12V 36D 1CT/10X5F

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.

Product data

General Information	
Cap base	GU5.3 [GU5.3]
Philips code	14598
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X
Light Technical	
Beam Angle (Nom)	36 °
Luminous intensity (max.)	800 cd
Rated beam angle	36 °
Correlated colour temperature (nom.)	3000 K
Color rendering index (nom.)	100
Luminous Flux in 90° Cone (Rated)	430 lm
Operating and Electrical	
Power (Rated) (Nom)	35 W
Lamp current (nom.)	2.92 A
Starting time (nom.)	0.0 s
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	B
Luminaire Design Requirements	
Cap base temperature (max.)	250 °C
Product Data	
Full product code	871150088593765
Order product name	Ess MR16 35W GU5.3 12V 36D 1CT/10X5F
EAN/UPC – product	8711500885937
Order code	88593765
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	924049617186
Net weight (piece)	0.032 kg
ILCOS Code	HRGI-50-12-GU5.3-35/36

Essential LV MR16

Dimensional drawing



Fighter 14598 35W GU5.3 12V MR16 36D

Product	D (max)	C (max)
Ess MR16 35W GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

