



Essential LV MR16

HAL-DICH 2Y 50W GU5.3 12V 36D 1CT/10X5F

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.


Product data

General Information	
Cap base	GU5.3 [GU5.3]
Philips code	14600
Burning Position	UNIVERSAL [Any/Universal]
ANSI code halogen	EXN
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X
Light Technical	
Technical Beam Angle (Nom)	36 °
Luminous intensity (max.)	1200 cd
Rated beam angle	36 °
Colour Temperature, horizontal (Nom)	3000 K
Colour Rendering Index,horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	50 W
Lamp current (nom.)	4.17 A
Starting time (nom.)	0.0 s
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	yes

Approval and Application	
Energy efficiency label (EEL)	B
Energy Consumption kWh/1000 h	53 kWh
Luminaire Design Requirements	
Cap base temperature (max.)	250 °C
Product Data	
Full product code	872790025244660
Order product name	Hal-Dich 2y 50W GU5.3 12V 36D 1CT/10X5F
EAN/UPC – product	8727900252446
Order code	25244660
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	924049717129
Net weight (piece)	0.032 kg
ILCOS Code	HRGI-50-12-GU5.3-50/36

Essential LV MR16

Dimensional drawing



Fighter 14600 50W GU5.3 12V MR16 36D

Product	D (max)	C (max)
Hal-Dich 2y 50W GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Photometric data

